

An aerial photograph of a river flowing through a dense forest. The river, with its vibrant blue-green water, cuts through a rocky landscape, creating a winding path through the green trees. The surrounding terrain is rugged, with patches of exposed rock and soil. The overall scene is one of natural beauty and industrial potential.

Demystifying Technical Excellence Of Grundfos' Industrial Solution

GRUNDFOS 

Possibility in every drop



Introduction to Grundfos iSOLUTIONS



Grundfos iSOLUTIONS brings the benefits of intelligent solutions to advanced pump systems and water technology



FAULT PREDICTION

Analysis of performance data to predict system failures

OPTIMISATION

Analysis of performance data and subsequent adjustment of system settings to optimize running settings

REMOTE CONTROL

Adjustment of power settings power, pressure, flow and see location of booster system through a remote device

ALERTS

Detection of abnormalities and failures of system and components through warnings and alerts and notification

MONITORING

Measurement of various pump performance parameters real time and display these as well as historical data

CONNECTIVITY

Prerequisite for the other digital building blocks

Our ambition for the future is to deliver advanced Grundfos iSOLUTIONS offerings available on your demand!

Key applications

-  Heating
-  Cooling
-  Temperature control
-  Boiler feed
-  Wash and clean
-  Ultrafiltration
-  Water treatment
-  Intake and distribution



Demo Unit



Item	Demo Unit
1	CMBE twin booster system demo
2	CR level & Temperature control
3	High pressure wash and clean
4	MGE motor suitcase



CR Level & Temperature Control Demo Unit

Application :
iBoiler

Control Mode:
Constant Level

Key Function:
- Stop @ min
speed
- Setpoint
Influence

Application :
Industrial Cooling

Control Mode:
i. Constant Diff
Temp
ii. Constant Temp

Key Function:
- Limit Exceed
Function
- Multi Temp
measurement






Stop @ min. speed

This function will stop the pump when it is running at minimum speed

- Set the delay time
- Set the restart speed to be 'X%' of nominal speed

In order not to overfill the boiler when right level has been reached, the feature named Stop @ Min Speed can be used.




Note: This function is meant for boiler systems without economizer

Setpoint Influence Function



The Setpoint Influence Function- Allows the pump to readjust the Setpoint based on the monitored input signal (sensors). It is most suitable for application which has multiple fluctuation of input signal (sensors).




Example: Water Level is 0.25m when steam output is 5m³/h. When it increases to 10m³/h, then the setpoint will auto readjust the Water Level to 0.30m. This is to avoid the increase of start-stop for the pump when the boiler burn faster than the incoming water into the tank.

Multiple Temperature measurement

E-pumps (with MGE) allows constant temperature operation in different ways.

Temperature sensors can be placed in the critical points in the application, this can either be single point measurements or using two single point transmitters to allow for running differential temperature control.

Temperature sensors can either be PT100/1000 or 4-20mA/0-10V.




Limit Exceed Function

This function to monitor a measured parameter or one of the internal values such as speed, motor load or motor current.

If a set limit is reached, a selected action can take place.
(E.g: pump stop, warning alarm, send relay, min speed , etc.)

Example:

In industrial cooling application it is important to not only control the water temperature to the cooling tower, but we also need to ensure the most efficient combination between cooling tower fan and pump operation.



So, to avoid energy waste and smooth operation , a Limit Exceed Function comes to play and send a relay signal to control the cooling tower fan

An aerial photograph of a deep, narrow mountain valley. The valley floor is covered in a dense forest of green coniferous trees. A bright blue river flows through the center of the valley, its water cascading over rocky ledges and creating white rapids. The surrounding slopes are steep and rocky, with patches of green vegetation and moss. The overall scene is rugged and natural.

Thank You !